

温度测试与调整

在温度测试前,应确保供水系统充分且有较高的温度。温控把手在37度位置时,打开龙头让水流出。进行温度测量,出厂时温度设定在36~38度范围内。如超出这个范围,要进行调整。调整的步骤如下:



温度稳定后,不要转动温控阀轴,安装温控把手,使温控把手的参考标识与数字37对齐。锁紧螺钉,安装把手上盖(图Fiq.5)。



Verification and Setting

Make sure that the water feeds of the faucet have reached their highest temperature by letting the water run sufficiently. With the selector in position 37°C, the temperature of the water coming out of the faucet must be within a range of 36°C and 38°C, as measured by a bath thermometer. If this is not the case, the installer can adjust the setting. Proceed with the setting as follows:


Uninstall handle kit. With the faucet on 'cold' normal water flow, slowly turn the temperature selector(always in the same direction) until water at 37°C is obtained. If the temperature goes over 38°C, go back to the 'cold' setting and set again.

When the temperature is stabilized, without turning the cartridge spindle, make sure the reference mark of the temperature handle aligned with the number 37. Tighten the screw, put on the handle plug. See fig. 5.


CARE AND MAINTENANCE


维护与保养


滤网垫片(18)可起到保护龙头的作用,但长时间使用后水垢或杂质可能会堵塞滤网降低水流量。如有类似情况发生,卸下龙头,用六角扳手(12mm)将底座(20,顺时针)拧下,取下螺母(19)、滤网垫片(18)和单向阀(17)。用热醋清洗滤网。然后按照图示装回。(注意:单向阀必须按原方向装回)。




拆卸前确保指示标识与数字37对齐。 拆卸把手组件(Fig.7),然后将螺母和塑料套卸下(Fig.8)。小心地卸下温控阀 (Fig.9)。用热醋进行清洗。清洗后,将塑料套和螺母(限位组件)装到温控阀上面,使塑料套的定位柱嵌入温控阀的限位槽内(Fig.10)。然后将塑料套的定定位柱与龙头本体内孔凹槽对齐,装入温控阀并锁紧螺母(Fig.11)。









The filters(18) protecting the faucet device may get obstructed and reduce water flow. When this happens, unscrew the bushes(20, left thread) by a wrench(12mm) and take out the nuts(19), filters(18) and the check valves(17) after removing the faucet. Clean the filters by soaking them in warm vinegar. Reinstall them as the figure.(Note: Check valves should reinstall as original orientation).

Very hard water can obstruct the filters protecting the thermostatic cartridge and reduce the flow of water. Please clean the cartridge as follows: Shut off the water supply of the faucet and open the water flow handle, then proceed to remove the cartridge. The cartridge is sensable, please be careful.

Make sure the reference mark is aligned with number 37 before your action. Remove the handle kit(Fig.7), unscrew the nut and stopper(Fig.8). Removing the cartridge cautiously(Fig.9). Clean the thermostatic cartridge by soaking it in warm vinegar. After cleaning, install the 'stop assembly' back on the cartridge, adjusting the stop pin into the notch (Fig.10). Install the assembly cartridge and stop in the body, adjusting the stop pin into the notch(Fig.11).

KOHLER® INSTALLATION INSTRUCTIONS



Wall-Mount Thermostatic

安装说明书

72641T 挂墙式恒温浴缸花洒龙头 72643T 挂墙式恒温花洒龙头

安装之前

所有的资料是按最新出版的产品资料编写而成。科 勒公司保留任何时候不经通知即可改变产品特性、 包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容,请把这些资料交给用户阅读。

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.

使用环境


- 1. 最小供水压力: 0.5bar(0.05MPa)。
- 2. 推荐冷热供水的静态压力: 3bar(0.3MPa)。
- 3. 如果供水压力大于5bar(0.5MPa), 安装减压阀。
- 4. 热供水温度最低: 50°C; 最高: 80°C。
- 5. 推荐的热供水温度: 65°C。
- 6. 温度的设定基本范围为: 20°C到50°C。
- 7. 安全限位温度: 40°C。
- 8. 冷热供水压力差不大于2bar(0.2MPa)。
- 9. 花洒最高使用环境温度: 60°C。请特别注意花洒同花洒连接的臂管必须远离加热器,否则可能损坏花洒及其密封件,甚至对使用者造成伤害。


OPERATION CONDITION

- 1. Minimum supply pressures: 0.5bar(0.05MPa).
- 2. Recommended supply static pressures: 3bar(0.3MPa) on hot and cold water.
- 3. Supply pressure greater than 5bar(0.5MPa): install a pressure reducer.
- 4. Hot water temperatures, minimum: 50°C, maximum:80°C.
- 5. Recommended hot water temperature: 65°C (energy-saving).
- 6. Setting range, approximately: 20°C to 50°C.
- 7. Safety stop at: 40°C.
- 8. Pressure difference between hot and cold supply: 2bar(0.2MPa) maximun..
- 9. The highest environment temperature for handspray & showerhead is 60°C. Please keep handspray, showerhead and the shower arm away from heater, or it may become damaged and cause injury to the user.

安装尺寸

ROUGH-IN DIMENSIONS





安装步骤

如何安装水龙头

为使安装顺利, G1/2"内螺纹管道配件 应已安装好。预留150mm的间距,保 持水平,不要凸出墙面。热供水管装 在左边。


在两个接头(1)涂上螺纹密封膏或缠绕 足以密封的密封胶带, 旋入冷热供水 管中。

调节两个接头,使其中心距为150mm 并保持同一水平。他们凸出墙面的尺 寸应该在40到45mm之间。将装饰罩 (2)旋入接头,紧贴墙壁。

将垫片(3)放入水龙头螺母(4)中,将螺 母旋到接头上,并用扳手(5)拧紧。

在锁紧螺母时,须用带状扳手或用软 布垫在普通扳手和螺母之间,以保护 镀层表面。

将垫片(6)安装在软管(8)与出水口(9)之 间。限流器(7)塞入手持花洒(10)进水 口。垫片安装在手持花酒与软管之 间。然后锁紧所有衔接螺母。



INSTALLATION

How to Install the Faucet

To perform installation, installer must provide G1/2" female supply fittings, spaced 150mm apart, horizontally and not extending beyond the finished wall surface. Hot supply pipe must be located on the left.

Install the two offset connectors(1) into the hot and cold supply pipes. Use appropriate thread sealants or thread tape on pipe threads.

Adjust the center-to-center distance between the connectors to 150mm and horizontally. They should extend 40 to 45mm beyond the finished wall. Thread the escutcheon(2) onto the connectors until they are against the finished wall.


Put washer(3) into nut(4) and tighten the nut with tool(5).

When tighten the nut, use strap wrench or soft cloth between product and regular wrench to protect the finish.

Put the washer(6) between hose(8) and shower outlet(9). Put the restrictor(7) into the handspray(10) inlet. Provide washer between the hose and handpray. Tighten all the connections.

如何安装托架

在墙面选一合适的位置来安装托架。 根据孔距在墙面标记钻孔的位置,依 据胀塞(11)直径打孔,安装胀塞。



How to Install the Bracket

Determine a suitable location on the finished wall to install the bracket. Mark bracket base mounting hole locations on the wall according to the dimension. Drill two holes on the finished wall, the holes should match the anchors(11). Install the anchors.

Tighten screws(12) to secure bracket base(13, flat side upward). Put the bracket(14) onto the bracket base and lock by stopper.

安装结果检查

确保所有衔接螺母都已锁紧。确保把 手处于关闭的位置。开启主水源,检 查是否有漏水。如有漏水,修理之。

INSTALLATION CHECKOUT

Ensure that all coupling nuts are tight and the water flow handle is in the close position. Turn on the main water supply, and check for leaks. Repair as needed.

浴缸花洒龙头:

取下手持花洒,用工具(15)卸下起泡器 组件。将流量把手旋转到开的位置, 慢慢旋转温控把手。让水流出约一分 钟,以清除杂质。关闭龙头,并装回 手持花洒和起泡器组件(16)。



assembly(16).

Bath & Shower Faucet

Remove the handspray and aerator by

tool(15). Turn the water flow handle to the "open" position, and slowly turn the

temperature selector. Run water through

remove any debris. Close the faucet, and

the faucet for about one minute to

reinstall the handspray and aerator

Remove the handspray. Turn the water flow handle to the 'open' position, and water through the faucet for about one faucet, and reinstall the handsprav.

Shower Faucet

slowly turn the temperature selector. Run minute to remove any debris. Close the

OPERATION INSTRUCTIONS

The temperature is set by slowly turning the temperature selector(right-hand

handle). For safety reasons, there is a

stop that limits temperature to 40°C. To

get a higher temperature, push the button and continue turning the temperature

Water flow is set by turning the left-hand

handle. There is also a water-saving

花洒龙头:

取下手持花洒, 打开水流把手, 慢慢 旋转温控把手。让水流出约一分钟, 以清除杂质。关闭龙头, 并装回手持 花洒。



使用说明


慢慢旋转温控把手即右把手, 调整温 度,安全限位温度为40度。如果想得 到更高的温度, 按住按钮继续旋转。

水流量是通过左把手来控制的。左把 手设有一个节水限位。如果想得到更 大的水流, 按住按钮继续旋转即可。

节水限位器的调整

如果节水限位的水流不满足需要,可 进行调整(Fig.4)。取下把手上盖,用 螺丝刀取下螺钉及把手组件。调整限 位器限位点的位置。如果要得到更大 的限位水流,逆时针调整限位点;如 果想得到较小的限位水流, 顺时针调 整限位点即可。

注意: 装回流量把手时, 先使流量阀 处于关闭位置,并且将按钮与本体另 一端的数字37对齐,装回把手,拧紧 螺钉, 安装把手上盖。




Plant setting position

stop. To obtain a higher flow rate, push the button and continue turning it.

Stopper Adjustment

selector.


If the flow can't meet the demand, it can be adjusted(Fig.4). Uninstall the handle kit and adjust the position of stopper. Turn the counter-clockwise to increase the flow rate; Turn clockwise to decrease the flow rate.



NOTE: When you reinstall the handle, make sure the flow valve in the 'close' position, the button of water flow handle should be aligned with the 37 mark. Tighten the screw. Put on the handle plug.

837392-D 2 837392-D 注意:确保拆卸、安装过程中,不要转动温控阀轴。如果不小心转动了阀轴,要调整阀轴使外齿上的圆孔标识与相邻的塑套上的凹槽对齐(Fig.12),或按前述方法调整。

安装温控把手, 使温控把手的数字37标识与本体圆形激光标识对齐, 拧紧螺钉。安装把手上盖。(Fig.13)



NOTE: Do not turn the cartridge when reinstall it. If you turned it without carefully, you should adjust it and be sure that the round mark is correctly in line with the groove(Fig.12), or readjust as per the steps of verification and setting.

Install the temperature selector(without turning the spindle). Align the reference number 37 mark on the temperature handle with the round laser mark on the body(Fig.13). Tighten the handle with the screw. Put on the handle plug.

清洗说明

适用于所有加工处理过的表面:以中性肥皂水清洗 镀层表面,再以干净的软布彻底擦干整个表面,许 多清洁剂,比如氨水、去污粉及洁厕灵等,会对电镀表面造成伤害,切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.


Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

837392-D **5**





72641T 挂墙式恒温浴缸花洒龙头 72643T 挂墙式恒温花洒龙头



837392-D **6**