

ALEO

Features

- · Brass construction
- Optimized sprayface and large nozzles with Katalyst, Air-induction for improved water coverage
- · Precise thermostatic valve with over-ridable temperature stop for added safety
- · Durable KOHLER finishes resist corrosion and tarnishing
- · Adjustable inlet fittings with 15mm tolerance
- · Adjustable inlet fittings with 15mm tolerance
- Includes 10" ultra thin round Katalyst Air Rainhead
- · Includes 110 mm Renew Organic 3-function handshower

Codes/Standards Applicable

Specified model meets or exceeds the following:

• EN 1111-1998 • QB 2806-2006 • GB 18145-2014

Installation Notes

· Install this product according to the installation guide.

THERMOSTATIC DUAL SHOWER COLUMN-DIRECT CONNECTION


97822T-9




Specified Model

Model	Description	Color/Finished
97822T-9	Aleo Thermostatic Dual Shower Column-Angular	Polished Chrome (CP)

For a full range of color finishes in your market please contact your local Kohler representative.






Note: 1. Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

2. Flow rates shown with supplied flow regulators installed.

Dimensions are approximate.

Unit: mm



Product Diagram