

# **ALEO**

## **Features**

- · Brass construction
- Optimized sprayface and large nozzles with Katalyst, Air-induction for improved water coverage
- · Leak-free ceramic disc valve with lifetime warranty
- · Durable KOHLER finishes resist corrosion and tarnishing
- · 200mm spout reach
- · Adjustable inlet fittings with 15mm tolerance
- Includes 8" ultra thin round Katalyst Air Rainhead
- · Includes 110 mm Renew Organic 3-function handshower

## **Codes/Standards Applicable**

Specified model meets or exceeds the following:

• GB 18145-2014 • EN 817-2008

#### **Installation Notes**

· Install this product according to the installation guide.


# 3 WAY SHOWER COLUMN-DIRECT CONNECTION 97825T-4





# **Specified Model**

Model	Description	Color/Finished
97825T-4	Aleo 3 Way Shower Column-Angular	Polished Chrome (CP)

For a full range of color finishes in your market please contact your local Kohler representative.








Note: 1. Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

2. Flow rates shown with supplied flow regulators installed.

Dimensions are approximate.

Unit: mm



**Product Diagram**