

BEFORE YOU BEGIN

安装之前

- Please read these instructions carefully to familiarize yourself with the required tools, materials, and installation sequences. Follow the sections that pertain to your particular installation. This will help you avoid costly mistakes. In addition to proper installation, read all operating and safety instructions.
- All information in these instructions is based upon the latest product information available at the time of publication. Kohler China reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.
- These instructions contain important care, cleaning, and warranty information—**please leave instructions for the consumer.**
- Before installation carefully inspect the new fixture for any signs of damage.
- The product complies with GB/T10357.4-2013, GB/T10357.5-2013, GB24977-2010, GB19510.1-2009, GB19510.14-2009 and GB7000.1-2015.



WARNING: Risk of electrical shock. A licensed electrician should make all electrical connections.



WARNING: Risk of electrical shock. Connect only to a circuit protected by a typical two-pole circuit breaker.



WARNING: Risk of electrical shock. Disconnect power before servicing.

- 请仔细阅读本指引，以便熟悉所需工具、材料及安装程序。请遵照适用的章节来安装本产品，以免安装失当导致不必要的损失。除了有关正确的安装方法之外，还务请详阅所有操作及安全指引。
- 本指引所载之一切资料，均以印刷时所有之最新产品情况为基础，科勒中国保留权利随时更改产品特性、包装或供应情况，恕不另行通知。
- 说明书包括重要的安装、清洁及保养方面的内容，**请把这些资料交给用户阅读，保管。**
- 安装之前，仔细检查产品是否有损伤。
- 本产品符合 GB/T10357.4-2013, GB/T10357.5-2013, GB24977-2010, GB19510.1-2009, GB19510.14-2009和GB7000.1-2015。



警告：有触电的危险。
请找合格的电工来进行所有的线路连接。



警告：有触电的危险。
仅能和双极型断路器保护的电路连接。




警告：有触电的危险。
工作之前先切断电源。

ACCESSORIS LIST

附件清单



Wall Anchors
入墙胶粒
5PCS (600镜柜)
6PCS (800、1000镜柜)



Top Clips
顶扣
3PCS



Screw ST3.5x35
盘头自攻螺钉 ST3.5x35
5PCS (600镜柜)
6PCS (800、1000镜柜)



Shelf Clip
嵌入式层板架
10PCS (600镜柜)
22PCS (800、1000镜柜)



Mounting Bar
承托条
1PCS



Side Mirror Kits
侧镜组件
2PCS



Glass Shelves
玻璃层板 532x115x6 mm
2PCS (600、1000镜柜)



Glass Shelves
玻璃层板 432x115x6 mm
2PCS (800镜柜)



Glass Shelves
玻璃层板 355x115x6 mm
3PCS (1000镜柜)



Glass Shelves
玻璃层板 255x115x6 mm
3PCS (800镜柜)




1247371
螺钉M4x10
5PCS

ROUGHING-IN


尺寸图

Reference Value
参考值


UNIT: mm
单位: 毫米




K-25237T-L/K-25237T-R



K-25238T



K-25239T



Kohler reserves the right to change marked dimensions without prior notice.
科勒公司保留随时变更图中标示尺寸的权利，无需另行通知。

ZHONGSHAN KOHLER SHOWER CO., LTD. NO13-1, XINGYE ROAD, ZHONGSHAN TORCH
DEVELOPMENT ZONE, ZHONGSHAN, GUANGDONG, CHINA POST CODE: 528437
中山科勒卫浴有限公司 广东省中山市中山火炬开发区兴业路 13-1 号 邮编: 528437


ELECTRICAL PARTS LIST

电器部件清单

Item 序号	Electrical Function 电器功能	Type Description 规格描述	Fixate Place 安装位置
1	Defogger 防雾膜	Input: DC12V, Pmax=15W	Back of outer-mirror 贴外镜背面
2	Lighting 灯具	Input: DC12V, Pmax=15W	Back of outer-mirror 贴外镜背面

CABINET INSTALLATION

柜体安装




INSTALLATION

安装


STEP1: Install mounting bar. Take out the mounting bar and put level.
Drill holes according to the hole spaces.
安装步骤一: 安装托条, 拿出托条, 水平放置, 按托条上的孔距进行钻孔。

STEP2: Fix the cabinet
安装步骤二: 固定柜体
1. Put the cabinet on the mounting bar.
1. 将柜体放在托条上。
2. Insert top clips from the center of the top.
Slide the clips to align with the drilled holes. Fix with screws.
2. 从中间缺口嵌入顶扣在柜顶, 滑动顶扣, 对准上一步骤的钻孔后, 用螺钉固定。




Adjust the door (only necessary if the door does not completely match the cabinet when it is closed).
调门体（当关门时门体和柜体不完全重合时，才需要调节）。

1. Open hinge cover before adjusting the door.
1. 门体调节前，先将铰链盖揭开。




2. Adjust the hinge as shown when necessary.
2. 门体不正时，可按如图所示调节铰链。



Install glass shelf 装玻璃层板


1. Insert the snap-in pins into the side holes.
1. 将嵌入式层板架插入两边侧孔。
2. Insert the glass shelf into the snap-in pins, insert the glass shelf vertically upwards and then rotate to horizontal position.
2. 将玻璃层板插入层板架，垂直往上穿入，再旋转水平后推入。



Adjust magnifying glass 调整放大镜


To adjust mirror height, slide up or down.
上下滑动，以调节镜子高度。

IMPORTANT! Rotate mirror in before closing the door.
重要：必须在柜门关闭前旋入镜子。




Install accessories and side mirror as shown.
镜柜配件及侧镜的安装：按图示位置进行安装。

1. Align the side mirror with the top and bottom of the cabinet.
Clean the back of the mirror.
1. 将侧镜与柜体边上下对齐，试装一下是否吻合，再将侧镜背面擦干净。
2. Peel off the double-sided tape and press onto the side mirror for 30 seconds.
2. 撕开侧镜支架上的双面胶面纸，贴上侧镜并按紧30秒。




Parts of the mirror cabinet:
镜柜各部件说明：




Installation of all parts of the mirror cabinet:
镜柜各部件安装说明:

- Slide the tray into a mounting groove at the bottom of the mirror cabinet, and push the tray to the side fixate place.
- 将托盘滑进镜柜底部的安装槽中，推至侧边安装位置。





- Hang the hair dryer holder and the hanger on the storage plate.
- 安装需要将吹风机支架，挂架挂在置物板上。





- Small iron tools can be attached to the magnetic chuck on the front side of the storage plate.
- 小的铁质工具可吸附于置物板正面的磁性吸盘。

Mirror cabinet inductive switch:
镜柜感应开关:

The lighting and defogger can be turned On/Off with the inductive switch at the lower-left corner of the mirror cabinet.
灯具和防雾膜可通过镜柜左下角的感应开关实现开关。



Power line access
电源线接入



Wire Input (three-core cable)
外部电源线输入 (三芯电缆线)
220V/50Hz

Fixture 接线座	Outlet 电源电线	Wiring Color 电线颜色
L	Hot 火线	Brown 棕色线
⊕	Ground 地线	Yellow & Green 黄绿色线
N	Neutral 零线	Blue 蓝色线

USER MAINTENANCE

日常维护

Warning! Risk of product damage.

The bathroom shall be kept in good ventilation. Clean the cabinet with water and soft cloth. Do not use detergent containing abrasive and chemical substance.

警告! 小心产品受损。

卫生间尽量保持空气畅通，镜柜只能使用蘸有清水的湿布擦拭，勿使用含研磨剂及化学物质的清洁剂。