

### Features

- Includes four 1.5 V AA batteries.
- Fixture-mount design.

### Material

- Brass construction.

### Technology

- Slow-closing piston technology.
- Electronic infrared sensor with TriPoint™ technology for accurate activation.

### Installation

- Intended for toilet installations with 1-1/2" spud coupling connection.

### Optional Accessories

- GP1118986 Flushometer Extension Kit
- K-10313 Flushometer 12" rough-in kit
- K-13716 24" Tailpiece



CSA B651

OBC


### Codes/Standards

ASME A112.18.1/CSA B125.1  
CSA B64  
CSA B125.3  
ASSE 1037/ASME A112.1037/CSA B125.37  
All applicable US Federal and State material regulations  
ICC/ANSI A117.1  
CSA B651  
OBC

### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

\*11-3/8" (289 mm) minimum with a  
6" (152 mm) critical level above the fixture



### Technical Information

All product dimensions are nominal.

Power source: Battery - DC, included

Fixture pressure max 80 psi (551.6 kPa)  
(static):

### Pressure and Supply Requirements

#### Fixture Supply Requirements

Max static pressure: 80 psi (551.6 kPa)

Min flowing pressure: 25 psi (172.4 kPa)

Min flow rate: 25 gpm (94.6 lpm)

### Notes

Install this product according to the installation guide.

OBC, CSA B651 compliant when installed to the specific requirements of these regulations.