

Features

- Digital control with easy-to-read icons and configurable touch screen.
- Control temperature, flow, and up to six shower outlets from a simple, intuitive interface.
- Turn the large KOHLER dial for easy temperature and flow rate adjustment.
- Nine user-definable presets let you save your favorite shower settings.
- Downloadable experiences provide spa-like ambience; available through the KOHLER Konnect® App.
- System warm-up and pause feature.
- Conserve water by enabling built-in eco mode, which limits use to only one outlet at a time.
- Available in multiple languages.
- Connect up to two controls within your digital shower system.
- Pair with the KOHLER Konnect® app for additional functionality and customization, including voice-control compatible with Amazon Alexa or Google Home.
- Requires an Anthem digital thermostatic valve (K-28209, K-28210, K-28211 or K-28212); sold separately.
- Pair with optional Anthem remote on/off button (K-28213); sold separately.



Codes/Standards

UL 1951
CSA C22.2 No. 68

KOHLER® Electronic Faucets, Valves, and Controls Five-Year Limited Warranty

See website for detailed warranty information.

Material

- Premium material construction for durability and reliability.

Installation

- Wall-mount.

Required Products/Accessories

K-28209 Two-port digital thermostatic valve

or

K-28210 Three-port digital thermostatic valve

or

K-28211 Four-port digital thermostatic valve

or

K-28212 Six-port digital thermostatic valve

Recommended Products/Accessories

K-28213 Remote on/off button for digital thermostatic valve

Included Components

Additional Components:









Cable


Fixing Kit

Mounting Bracket

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant® Polished Nickel
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass
	RGD	Vibrant Rose Gold



Technical Information

All product dimensions are nominal.

Drain included: No
Cable length: Data, 32 ft (9.8 m)
Max. Ambient temp: 104°F (40°C)

Notes

Install this product according to the installation instructions.