



**Undertone®**  
Under-mount Kitchen Sink  
**K-3166**

**Features**

- 45-inch minimum base cabinet width.
- 18-gauge stainless steel.
- Under-mount.
- Rounded bowls.
- Triple compartment.
- 9-1/2" (241 mm) deep left bowl, 7-1/2" (191 mm) deep right bowl and 5-1/2" (140 mm) deep center bowl.
- SilentShield® sound-absorption technology offers quieter performance.
- 41-5/8" (1057 mm) x 20-1/8" (511 mm)

**Optional Accessories**

- K-3278 Cutting Board
- K-3291 Colander
- K-6139 Sponge Caddy

**Components**

- Product includes:  
91915 Hardware Kit




**Codes/Standards**

ASME A112.19.3/CSA B45.4

**Lifetime Limited Warranty for  
KOHLER® Stainless Steel Sinks**

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Bowl configuration:	Two equal bowls and center bowl
Installation:	Under-mount
Bowl area (Left):	Length: 14" (356 mm) Width: 18" (457 mm) Bowl depth: 9-1/2" (241 mm)
Bowl area (Center):	Length: 9" (229 mm) Width: 15" (381 mm) Bowl depth: 5-1/2" (140 mm)
Bowl area (Right):	Length: 14" (356 mm) Width: 18" (457 mm) Bowl depth: 7-1/2" (191 mm)
Drain hole:	3-5/8" (92 mm)
Template:	1047579-7, required, included

## Notes

Install this product according to the installation instructions.