



## Undertone® Preserve®

Under-mount Kitchen Sink  
K-3171-HCF

### Features

- 36-inch minimum base cabinet width.
- Double equal bowls.
- 9-1/2-inch depth provides generous workspace.
- No faucet holes.
- The innovative Preserve™ sink resists scratching and withstands the everyday wear and tear your sink endures, keeping it looking newer longer.
- Rear drain increases workspace in the sink and storage space underneath.
- SilentShield® sound-absorption technology offers quieter performance.
- Includes 1 sink rack.
- Includes installation hardware.

### Material

- 18-gauge stainless steel.

### Installation

- Under-mount

### Recommended Accessories

- K-6388 Sink Rack
- K-3294 Cutting Board
- K-8801 Sink Strainer

### Components

Additional included component/s: Bottom Bowl Rack.




### Codes/Standards

ASME A112.19.3/CSA B45.4

### Lifetime Limited Warranty for KOHLER® Stainless Steel Sinks

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Bowl configuration: Double equal

Installation: Under-mount

Bowl area (Left): Length: 14" (356 mm)  
Width: 15-3/4" (400 mm)  
Bowl depth: 9-1/2" (241 mm)  
Water depth: 9-1/2" (241 mm)

Bowl area (Right): Length: 14" (356 mm)  
Width: 15-3/4" (400 mm)  
Bowl depth: 9-1/2" (241 mm)  
Water depth: 9-1/2" (241 mm)

Drain hole: 3-3/4" (94 mm)

Template: 1221369-7, required, included

### Notes

Install this product according to the installation instructions.

Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.