



Undertone®

Under-mount Kitchen Sink
K-3356

Features

- Minimum base cabinet width: 36" - 39" (36" may require cabinet modifications).
- 9-1/2-inch left depth and 7-1/2-inch right depth.
- No faucet holes.
- SilentShield® sound-absorption technology offers quieter performance.
- Includes installation hardware.

Material

- 18-gauge stainless steel.

Installation

- Under-mount
- Extra-large/ medium bowls.

Recommended Accessories

- K-6389 Sink Rack
- K-3278 Cutting Board
- K-3291 Colander
- K-6390 Sink Rack
- K-8801 Sink Strainer




Codes/Standards

ASME A112.19.3/CSA B45.4

Lifetime Limited Warranty for KOHLER® Stainless Steel Sinks

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Bowl configuration:	Offset X-large/small
Installation:	Under-mount
Bowl area (Left):	Length: 17-7/8" (454 mm) Width: 17-7/8" (454 mm) Bowl depth: 9-1/2" (241 mm) Water depth: 9-1/2" (241 mm)
Bowl area (Right):	Length: 13-3/4" (349 mm) Width: 15-3/8" (391 mm) Bowl depth: 7-1/2" (191 mm) Water depth: 7-1/2" (191 mm)
Template:	1217909-7, required, included

Notes

Install this product according to the installation instructions.

Minimum base cabinet width 36" - 39" (36" may require cabinet modifications). Consult an installer for confirmation.