

### HANDSHOWER SET K-76399T

#### Features

- Push button, 3-function handshower
- 130 mm spray-plate diameter
- Katalyst air-induction technology
- Includes 1.5 m shower hose
- Includes handshower bracket with angle adjustment

#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552
- GBT 23447-2009

#### Installation Notes


Install this product according to the installation guide.



#### Specified Model


Model	Description	Color/Finished
K-76399T	Rainduet multi-function handshower with hose and bracket	CP: Polished Chrome

For a full range of color finishes in your market please contact your local Kohler representative



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.  
Unit: mm



Product Diagram

### คุณลักษณะ

- ปุ่มปรับระดับน้ำหัวฝักบัว 3 ระดับ
- หัวฝักบัวขนาด 130 มม.
- เทคโนโลยีหัวฝักบัวแคตทาลิส
- พร้อมสายฝักบัวยาว 1.5 เมตร
- พร้อมขอแขวนฝักบัวปรับระดับ

### มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- มอก. 2066-2552
- GBT 23447-2009

### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


## ชุดฝักบัวสายอ่อน K-76399T



### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-76399T	ชุดฝักบัวสายอ่อน 3 ระดับ พร้อมสายอ่อนและขอแขวน รุ่นเรนดูเอท	CP: สีโครมเงา


ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์