

### RECESSED SHOWER VALVE-COLD WATER ONLY K-99258X

#### Features

- Brass construction
- Includes a 35 mm ceramic valve cartridge for improved flow at lower pressures
- Handle is lift & turn activation
- Easy sealant-free trim installation


#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- N/A


#### Installation Notes

Install this product according to the installation guide.



#### Specified Model


Model	Description	Color/Finished
K-99258X-4CD	Singulier recessed shower valve-cold water only	CP: Polished Chrome



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm




Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

#### Product Diagram

### วาล์วเปิด-ปิดน้ำเย็นแบบก้านโยก ชนิดฝังผนัง

# K-99258X



#### คุณลักษณะ

- ผลิตจากทองเหลือง
- พร้อมเซรามิกวาล์วขนาด 35 มม. ช่วยเพิ่มประสิทธิภาพ อัตราการไหลของน้ำที่ใช้แรงดันต่ำ
- โยกและหมุนเพื่อใช้งาน
- ติดตั้งง่าย

#### มาตรฐาน

คุณสมบัติตามมาตรฐาน


- ไม่ระบุ

#### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

#### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-99258X-4CD	วาล์วเปิด-ปิดน้ำเย็นแบบก้านโยกชนิดฝังผนัง รุ่นซิงกูลิเยร์	CP: สีโครมเงา




กราฟแสดงอัตราการไหล

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

#### ภาพแสดงผลิตภัณฑ์