


Features

- Metal construction
- One-piece faucet, self-contained ceramic disc valve allows both volume and temperature control
- Response™ technology allows hands-free operation to turn faucet on and off
- DockNetik™ ensures a secure sprayhead fit
- Promotion™ technology with nylon hose and ball joint for easy operation
- Two-function sprayhead with touch control for spray and aerated stream settings
- Temperature memory allows faucet to be turned on and off at any temperature setting
- Flexible connections for easy installation
- 290° spout rotation
- For single-hole installation
- 1.8 gallons (6.8 L) per minute maximum flow rate at 60 psi (4.1 bar)
- Meets CalGreen requirements for kitchen faucets

**ELECTRONIC PULL-DOWN KITCHEN SINK FAUCET
K-72218**

ADA



Codes/Standards Applicable

Specified model meets or exceeds the following at date of manufacture:

- ADA
- ICC/ANSI A117.1
- ASME A112.18.1/CSA B125.1
- Energy Policy Act of 1992
- NSF 61
- All applicable US Federal and State material regulations

Colors/Finishes

- CP: Polished Chrome
- VS: Stainless Steel

Accessories

- NA: None applicable

Specified Model

Model	Description	Colors/Finishes	
K-72218	Electronic pull-down kitchen sink faucet	<input type="checkbox"/> CP	<input type="checkbox"/> VS
K-72218-B7	Electronic pull-down kitchen sink faucet with black accents	<input type="checkbox"/> CP	<input type="checkbox"/> VS

Product Specification

The electronic pull-down kitchen sink faucet shall be of metal construction. Product shall have a one-piece, self-contained ceramic disc valve, which allows both volume and temperature control. Product shall feature Response technology, which allows hands-free operation to turn faucet on and off and DockNetik, which ensures a secure sprayhead fit. Product shall feature Promotion technology with nylon hose and ball joint for easy operation. Product shall have a two-function sprayhead with touch control for spray and aerated stream settings. Product shall feature temperature memory, allowing the faucet to be turned on and off at any temperature setting. Product shall feature 290° spout rotation and flexible connections for easy installation. Product shall be for single-hole installation. Product shall feature a 1.8 gallon (6.8 L) per minute maximum flow rate at 60 psi (4.1 bar). Product shall meet CalGreen requirements for kitchen faucets. Pull-down kitchen sink faucet shall be Kohler Model K-72218-____-____.

SENSATE™


Optional Accessories			
1012715	Deep roughing-in kit – provides an additional 2" (51 mm) assembly depth		<input type="checkbox"/> NA
1167289	Low flow kit – reduces maximum flow to 1.5 gpm (5.7 L) at 60 psi (4.1 bar)		<input type="checkbox"/> NA
1167290	High flow kit – increases maximum flow to 2.2 gpm (8.3 L) at 60 psi (4.1 bar)		<input type="checkbox"/> NA
1203620	10' (3 m) Power supply extension cable, 12 V DC		<input type="checkbox"/> NA
1209172	3-hole escutcheon kit	<input type="checkbox"/> CP	<input type="checkbox"/> VS

Installation Notes

Install this product according to the installation guide.

REQUIRED: Unswitched power outlet (120 V AC) located below the sink and within 5' (1.5 m) of the control box.
(Garbage disposals typically use switched outlets and are not recommended.)

ADA compliant when installed to the specific requirements of the regulation.



Product Diagram