

## **APPLICABLE STANDARDS**:-

1) D300\_001: KITCHEN SINK & LAVATORY CUTOUT TEMPLATE DESIGN.

NOTES 1 SHEET SIZE = A1 (ALTERNATE SHEET SIZE 23"x36")

PRINT AREA = 670x515 mm (26.35"x20.24")

- 3) PAPER MATERIAL : MAPLITHO PAPER ,  $100 \pm 5$  GSM
- 4) PRINTING COLOR: BLACK
- 5) SAMPLE COPY TO BE APPROVED BY KOHLER INDIA ENGINEERING TEAM PRIOR TO PRODUCTION.
- 6) TITLE BLOCK & NOTES OUTSIDE PRINT AREA(2) SHOULD NOT TO BE PART OF PRINTING.
- 6) THE ARTWORK MUST NOT BE SCALED. MUST BE PRINTED ON 100% (1:1) SCALE.

								GRADE : <b>REFER NOTES</b>				
										COLOR/FIN	NISH : RE	FER NOTES
	ALL DIMENSIONS IN MM						DIMENSIONING AND TOLERANCING PER ASME YI4.5M-1994					
							TOLERANCES	APPROVED	ARUN B	04.01.17	04.01.17	SCALE 1:1
							UNLESS /	DRAWN	DATE	CHECKED	DATE	DWG
							OTHERWISE SPECIFIED	MW	04.01.17	JAYESH	04.01.17	$\land \land \bigcirc \mid$
								DO	NOT SCALE DR	AWING	A.i.	SIZE
-							(SEE TOLERANCE TABLE)		KOHLER	N ®	RD ANGLE F	PROJECTION
								NOHLEK	INDIA CORP. P	V I. L I D.		
							THIS DRAWING IN DESIGN AND DETAILS	DESCRIP	TION			
	1	В	MW	ARUN B	SEE PCI #IN1601693	3 04.01.17	IS THE PROPERTY OF KOHLER CO. AND MAY	тс	MOLATE / INICT	ALL ATION	INICTOLIC	TION
	1	Α	VW	ARUN B	SEE PCI #IN1601268	20.10.16	NOT BE USED EXCEPT IN CONNECTION WITH		MPLATE / INST.	ALLATION	INSTRUC	TION
	SHT	SYM	ВҮ	APPROVED BY	DESCRIPTION	DATE	KOHLER CO. WORK. ALL RIGHTS OF	D.W.O. 11.0	128819	0 10101		SHT
			D١	WG REVISI	ON RECORD	•	DESIGN OR INVENTION ARE RESERVED.	DWG. NO	120019	3-1110 1		1 OF 1
$\stackrel{-}{\nearrow}$												