

### Features

- Touchless on/off with a wave of your hand
- For use with cold water line only
- Battery-powered
- 5-5/16" (135 mm) spout reach
- 0.53 gpm (2.0 lpm) maximum flow rate at 43.51 psi (3.0 bar)
- Includes installation hardware

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Deck-mount
- Single-hole installation
- G-1/2 water supply inlet
- Drain sold separately



### Codes/Standards

None Applicable


### KOHLER® Electronic Faucets, Valves, and Controls Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome



### Technical Information

All product dimensions are nominal.

Power source: Battery - DC, included

#### Faucet:

Flow rate: 0.5 gal/min (1.9 l/min)

Pressure: 45 psi (3.1 bar)

Drain included: No

Drain with overflow: No

#### Spout:

Spout reach: 5-5/16" (135 mm)

### Notes

Install this product according to the installation instructions.