

Features

- A sleek, black glass finish dual flush plate that is easy to clean
- Requires 2D batteries for operations which are accessible for replacement when required and has a manual override.
- Hygiene flush: Activate for automatic flushing every 4 hours, especially useful for public areas.
- Nightlight technology illuminates flush plate for 7 hours to aid flushing in the dark.
- Cleaning mode deactivates flush actuation for easy maintenance and cleaning
- Adjustable sensing distance

Material

- Glass.

Required Accessories


Pneumatic Air Actuation Assembly – 1278771

(needed in case of mechanical tank/pneumatic tank older than June 2019)

Spare Information

DC glass cover assy	1348760
Indian faceplate asm	1348759

*for complete spare part list, refer the installation instructions



KOHLER® Limited Warranty

See website for detailed warranty information
www.kohler.co.in/warranty



Available Colour/Finishes

Colour tiles intended for reference only.

Colour	Code	Description
■	1	Black

Package Content

1 touchless faceplate, 1 control assembly, 1 battery box,
1 Installation Instructions & 1 Warranty Card.



Technical Information

All product dimensions are nominal.

Model	24146IN-7
Power	2 'D' size Alkaline Batteries (3V DC) (not provided)
	Consumption:< 21mAh/full flush cycle
	Life: Minimum 10000 cycles*
User Sensing Distance	Default: 70cm
	Adjustable: 70cm-100cm
Flushing Actuation Sensing Distance	0.5-10.2cm
Flushing Actuation Confirmation Time	0.5s
Refilling Duration Indicator	Full Flush: Adjustable(25s-300s)
	Half Flush: 60% of Full Flush Time
Night Light	Default: Off
Hygiene Flush	Default: Off
Manual Flush Button	Yes (Behind Glass Panel)
User Manual	1348773-IN2

Notes

- Install this product according to the installation instruction.

* T&C depending on usage

** - indicates WC mounting dimensions.

Customer Care: 1800-103-2244 (Toll Free) & +91-124-4319685 / 86
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current Specification Sheet, go to www.kohler.co.in

THE BOLD LOOK
OF **KOHLER®**