

Features

- Single lever handle allows for both volume and temperature control
- Unique rear handle mounting creates floating effect and simplifies cleaning
- Available in a range of dazzling finishes
- 5-1/2" (140 mm) spout reach
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- Preattached flexible supply lines simplify installation



Codes/Standards

None Applicable


KOHLER India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant™ French Gold
	BL	Matte Black
	RGD	Vibrant Rose Gold



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 3.48 gal/min (13.2 l/min)

Pressure: 45 psi (3.1 bar)

Drain included: No

Drain with overflow: No

Spout:

Spout reach: 5-1/2" (140 mm)

Handle clearance: 1-1/8" (29 mm)

Notes

Install this product according to the installation instructions.