

### Features

- Diverter spout
- Available in a range of dazzling finishes
- 6-9/16" (167 mm) spout reach
- 4.48 gpm (17 lpm) maximum flow rate at 43.5 psi (3 bar)

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Wall-mount
- G 1/2 inlet connection



### Codes/Standards

None Applicable


### KOHLER India Faucet Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant™ French Gold
	BL	Matte Black
	RGD	Vibrant Rose Gold



### Technical Information

All product dimensions are nominal.

Drain included: No

### Notes

Install this product according to the installation instructions.