

Features


- Two-function pull-down sprayhead allows you to switch from aerated stream to powerful ring spray
- ProMotion™ technology's light, quiet braided hose and swiveling ball joint make the pull-down sprayhead easier and more comfortable to use
- High-arch gooseneck spout offers superior clearance for filling pots and cleaning
- Single-handle operation facilitates flow and temperature control
- 2.4 gpm (9.1 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation



Codes/Standards

None Applicable


KOHLER India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|---|------|-----------------|
|  | CP | Polished Chrome |



Technical Information

All product dimensions are nominal.

Drain included: No

Spout:

Spout reach: 8-3/8" (213 mm)