

### Features

- Single-function handshower delivers a full, consistent spray, regardless of water pressure.
- Infinity provides three spray experiences in one: strong-rinsing (top), massaging (middle), and broad coverage (lower).
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup.
- Optimized sprayface for maximum performance.
- 1.75 gpm (6.6 lpm) maximum handshower flow rate at 45 psi (3.1 bar).
- G 1/2 connection.

### Material


- Premium material construction for durability and reliability.
- KOHLER finishes resist corrosion and tarnishing.

### Installation

- Requires shower hose (sold separately).
- Bracket or sidebar required for wall-mount installation.
- Deck-mount holder required for deck-mount installation.

### Water Conservation & Rebates

- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System.



### Codes/Standards






ASME A112.18.1/CSA B125.1



### KOHLER India Faucet Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color   | Code | Description             |
|---|------|-------------------------|
|  | CP   | Polished Chrome         |
|  | AF   | Vibrant® French Gold    |
|  | BV   | Vibrant® Brushed Bronze |
|  | BL   | Matte Black             |
|  | RGD  | Vibrant Rose Gold       |



### Technical Information

All product dimensions are nominal.

#### Handshower:

Rated maximum flow: 1.75 gal/min (6.6 l/min)  
Pressure: 45 psi (3.1 bar)