

### Features


- Oblong single-function linear body spray delivers 14 twirling Deep Massage streams, targeting sore muscles to ease away aches and pains.
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup.
- Low-profile design complements any decor.
- 2.5 gpm (9.5 lpm) maximum flow rate at 45 psi (3.1 bar).

### Material

- Durable material construction.
- KOHLER finishes resist corrosion and tarnishing.

### Installation

- G 1/2 inlet connection.
- Semi-recessed into wall.



### Codes/Standards






ASME A112.18.1/CSA B125.1


### KOHLER India Faucet Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	RGD	Vibrant Rose Gold



### Technical Information

All product dimensions are nominal.

Drain included: No