

### Features

- Vitreous China
- With Overflow
- Above counter

### Recommended Accessories

- Bottle Trap (75823IN)
- Drain with Overflow (45432IN)



Material	Description
99858IN-4-CP	BEITOU SINGLE CONTROL TALL LAV FAUCET
97347IN-4-CP	AVID SC TALL LAV FAUCET WITH DRAIN
73053IN-4-CP	COMPOSED SC JOYSTICK TALL LAV FCT. W/D
73159IN-7-CP	COMPOSED SC SIDE MOUNT TALL LAV FCT. W/D
10861IN-4ND-CP	SINGULIER SINGLE LEVER TALL LAV FAUCET
72337IN-4ND-CP	ALEO+ TALL LAV FAUCET W/O DRAIN
72298IN-4-CP	ALEO TALL LAV FAUCET W/ DRAIN
37334IN-4-CP	STRAYT TALL PILLAR TAP
11546IN-4-CP	SINGULIER TALL PILLAR LAVATORY FAUCET
20071IN-4-CP	ALEO+ PILLAR TAP, TALL
20070IN-4-CP	ALEO PILLAR TAP, TALL


### KOHLER® Ten-Year Limited Warranty

See website for detailed warranty information.

### Available Color/ Finishes

Color tiles intended for reference only

Color	Code	Description
	0	White



### Notes

Install this product according to the installation instructions.

Product does have an overflow.

\*Spout must be 3.9" (99mm) long (min) for adequate clearance into the bathroom sink.

NOTICE: Counter cutting should be done using the cut-out template provided with the product. Kohler is not responsible for any cutout errors.

## Technical Information

All Product Dimensions are nominal

Lavatory configuration	Single
Installation	Above Counter
Bowl area	Length: 23 5/8" (600 mm) Width: 16 1/8" (410 mm) Height: 7 1/16" (179 mm) Depth: 5" (127 mm)
Drain hole	Ø41.65 - 46.5 mm
Template	1322971-K7