


### Features

- Dual flush
- Pneumatic Actuation, fewer parts
- Adjustable flushing volume with no effect on flow rate
- Adjustable Flow rate
- Water supply shut-off provision
- Pneumatic time delay delivers superior flush accuracy & repeatability
- Replaceable dual stage In-Line filter made of Stainless Steel
- Actuation force less than 22 N
- Remote installation possible
- Brass Inlet connection
- Removable valve body for easy maintenance
- Back pressure vacuum breaker
- Chlorine-Chloramine resistant rubber seals
- Made of high grade molded plastic & brass
- WC connection set includes Height adjustable trap, Bowl Inlet pipe, & construction Plug
- 4 inch wall installation
- Easy to install



### Technical Specifications

Inlet Size	G 1 ¼ inch
Pipe Line requirements	DN32 PVC/GI, DN40 CPVC
Pressure Requirement (Static Pressure)	1 bar to 6 bar
Flow rate	1.7 ~ 1.9 LPS @ 0.5 bar
Flush Volume	3/6 L
Water Temperature	4°-45° C
Wall Size	4 inches
Valve Body dimensions	222 x 179 x 87 mm
Faceplate dimensions	200 x 140 x 8 mm

### Compatible Bowls

Recommended to install with Kohler toilets. Flow rate & volume to be adjusted as per site requirements

TOLL FREE: 1800-103-2244

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.co.in](http://www.kohler.co.in)

©Kohler Co. Jan/2017



THE BOLD LOOK  
OF **KOHLER**®

### Compatible Faceplates

DESCRIPTION	SKU CODE
SOFTPRESS PNEUMATIC FACEPLATE	24555IN-P-**


### Available Color/ Finishes

Color tiles intended for reference only

Color	Code	Description
	CP	Polished Chrome
	AF	French Gold

### KOHLER® 10-Year Limited Warranty

See website for detailed warranty information.



TOLL FREE: 1800-103-2244

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.co.in](http://www.kohler.co.in)

©Kohler Co. Jan/2017

THE BOLD LOOK  
OF **KOHLER**®