

Features

- Vitreous China
- Without Overflow
- Above counter
- Large wash area



Recommended Accessories

- Bottle Trap (75823IN-CP)
- Grid Drain without Overflow (20746IN-CP)
- Ceramic Drain without Overflow (20740IN-0)

Material	Description
99858IN-4-CP	BEITOU SINGLE CONTROL TALL LAV FAUCET
97347IN-4-CP	AVID SC TALL LAV FAUCET WITH DRAIN
73053IN-4-CP	COMPOSED SC JOYSTICK TALL LAV FCT. W/D
73159IN-7-CP	COMPOSED SC SIDE MOUNT TALL LAV FCT. W/D
10861IN-4ND-CP	SINGULIER SINGLE LEVER TALL LAV FAUCET
72337IN-4ND-CP	ALEO+ TALL LAV FAUCET W/O DRAIN
72298IN-4-CP	ALEO TALL LAV FAUCET W/ DRAIN
37334IN-4-CP	STRAYT TALL PILLAR TAP
11546IN-4-CP	SINGULIER TALL PILLAR LAVATORY FAUCET
20071IN-4-CP	ALEO+ PILLAR TAP, TALL
20070IN-4-CP	ALEO PILLAR TAP, TALL


KOHLER® Ten-Year Limited Warranty

See website for detailed warranty information.

Available Color/ Finishes

Color tiles intended for reference only

Color	Code	Description
	0	White



Notes

Install this product according to the installation instructions.

Product does not have an overflow.

*Spout must be 3.9" (99mm) long (min) for adequate clearance into the bathroom sink.

NOTICE: Counter cutting should be done using the cut-out template provided with the product. Kohler is not responsible for any cutout errors.

Technical Information

All Product Dimensions are nominal

Lavatory configuration	Single
Installation	Above Counter
Bowl area	Length: 35 1/32" (890 mm) Width: 15 5/8" (397 mm) Height: 5 1/2" (139 mm) Depth: 4 1/2" (114 mm)
Drain hole	Ø41.65 - Ø46.5 mm
Template	1293912-IN7