

Features

- Brass construction.
- Wall-mount installation.
- Single-handle.
- Lever handle.
- Stationary spout.
- Less drain.
- Requires single-handle ceramic valve [K-307-K].
- Available with an 8-1/4" (210 mm) spout from wall to center of drain.
- 1.5 gal/min (5.7 l/min) maximum flow rate [max at 60 psi (4.14 bar)].

Required Accessories

K-307-K Wall-mount Bathroom Sink Valve

Optional Accessories

K-7114
K-7124
K-7127
K-7129



ADA

Codes/Standards

ASME A112.18.1/CSA B125.1

NSF 61

NSF 372

EPA WaterSense®

ADA

ICC/ANSI A117.1



All applicable US Federal and State material regulations


KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BN	Vibrant® Brushed Nickel



Technical Information

All product dimensions are nominal.

Spout reach: 8-1/4" (210 mm)

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Pressure: 60 psi (4.1 bar)

Notes

Install this product according to the installation guide.

Install the wall-mount valve according to the valve installation guide.

One 1-7/8" (48 mm) diameter cutout hole is required for the spout. One 1-7/8" (48 mm) diameter cutout hole is required for the handle.

ADA compliant when installed to the specific requirements of these regulations.