


### WALL-HUNG TOILET WITH EXPOSE TANK K-17661IN

#### Features

- Vitreous china
- Round bowl
- Silicone rubber flapper
- 0.8 gpf (3 lpf)/1.6 gpf (6 lpf)
- Wash down flushing system
- Wall-Hung with expose tank
- 3-1/8" (8.0 cm) glazed trapway
- Includes seat and cover
- Includes satin chrome top push button dual flush
- 3.78" (9.6 cm) x 4.15" (10.6 cm) water area



#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19
- EN 997

#### Colors/Finishes

- 0 : White
- Other : Refer to Price Book for additional colors/finishes

#### Accessories:

- SC: Satin Chrome
- Other : Refer to Price Book for additional colors/finishes

#### Specified Model

Model	Description	Colors/Finishes	
K-17661IN	Odeon wall-hung toilet with expose tank	<input type="checkbox"/> 0 white	<input type="checkbox"/> Other_____

#### Product Specification:


The Odeon wallhung toilet with expose tank shall be made of vitreous china. Toilet shall be 0.8 gallons (3 L) / 1.6 gallons (6 L) with wash down system, 3-1/8" (8.0 cm) glazed trapway and silicon flapper. Toilet shall include seat, cover. The toilet shall have 3-3/4" (9.6 cm) x 4.1/8" (10.6 cm) water area. Toilet shall be Kohler model K-17661IN-\_\_\_\_\_.

## Technical Information

Fixture:	
Configuration	2-piece, wall-hung with expose tank, round bowl
Water per flush	0.8 gallons (3 L) / 1.6 gallons (6 L)
Passageway	3-1/8" (8.0 cm)
Water area	3-3/4" (9.6 cm) x 4-1/8" (10.6 cm)
Water depth from rim	8-3/4" (22.2 cm)
Seat post hole centers	6-1/8" (15.5 cm)
Included Components:	
Bowl	K-17662
Tank	K-17663
Tank cover	1065187
Seat	K-8741X
Top push button	1035417-SC

## Installation Notes

Install this product according to the installation guide.



**Product Diagram**