

Features


- Katalyst air-induction spray assures optimum coverage and comfort
- Precision flow control meets all user needs regardless of your home's water pressure
- Ergonomic, easy clean design

Material

- Premium metal body
- Anti-bacterial silicone material

Installation

- Includes 1.2m flexible hose



Codes/Standards

None Applicable


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	CP	Polished Chrome
--	----	-----------------



Technical Information

All product dimensions are nominal.

Sidespray:

Flow rate: 2.77 gal/min (10.5 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: No

Notes

Install this product according to the installation instructions.