

### Features

- Single-function showerhead with 48 nozzle 5" (127 mm) diameter sprayface.
- Single-function showerhead with Katalyst® air-induction technology.
- Optimized sprayface for maximum performance.
- 2.5 gpm (9.5 lpm) maximum flow rate at 45 psi (3.1 bar).
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup.
- 1/2" - 14 NPT connection.
- Coordinates with other products in the Parallel collection.

### Material

- Premium material construction for durability and reliability.
- KOHLER finishes resist corrosion and tarnishing.

### Installation

- Wall-mount.

### Recommended Products/Accessories

K-7397 Shower Arm and Flange



### Codes/Standards


ASME A112.18.1/CSA B125.1  
DOE - Energy Policy Act 1992


### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BN	Vibrant® Brushed Nickel
	BL	Matte Black



### Technical Information

All product dimensions are nominal.

Drain included: No

### Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Pressure: 45 psi (3.1 bar)

### Notes

Install this product according to the installation instructions.