

Features

- Unique articulated-joint design directs water to any angle and folds out of the way when not in use.
- Single 1-5/16" (33 mm) diameter remote joystick lever handle is simple to use and makes adjusting water temperature easy.
- Ceramic disc valves exceed industry longevity standards, ensuring durable performance for life.
- Integral sprayhead provides laminar flow or aerated spray at the touch of a button
- Variable spout reach from less than 2" (51 mm) to over 13" (330 mm)
- 1.8 gallons (6.8 L) per minute maximum flow rate at 60 psi (4.1 bar)
- Meets CalGreen requirements for kitchen faucets.

Material

- Premium metal and carbon fiber construction.
- KOHLER finishes resist corrosion and tarnishing.

Installation

- 2-Hole Deck-mount
- Flexible supply lines and installation ring simplify installation.

Optional Accessories

1191733 Deep Rough-in Kit



ADA

CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF 61

NSF 372

All applicable US Federal and State material regulations

DOE - Energy Policy Act 1992

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

CSA B651

OBC

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color Code Description



CP Polished Chrome

VS Vibrant® Stainless

