






KOHLER®

ALEO







	Bar
	$0.5 < 3 < 6$
	°C
	$55 < 60 < 65$



E72352-**





E72286-**



E72287-**




1




E72352-**

E72286-**

2




3




E72287-**

2





3












E72352-**


E72286-**

4









KOHLER®

US

Kohler Co.
444 Highland Drive
Kohler, WI 53044
☎ 1 800 456 4537
www.kohler.com

GB

Kohler UK
Cromwell Road, Cheltenham,
Gloucestershire GL52 5EP
☎ +44 (0) 800 001 4466
www.kohler.co.uk