












KOHLER®

ALEO







	P	Bar	0.5 < 3 < 6
	T	°C	55 < 60 < 65




72275D-**
72277D-**




72279D-**




72278D-**




72298D-**
72299D-**




72288D-**



72351D-**




72283D-**






72282D-**



1







2






2






2





2





2




3



3





KOHLER®

US

Kohler Co.
444 Highland Drive
Kohler, WI 53044
☎ 1 800 456 4537
www.kohler.com

GB

Kohler UK
Cromwell Road, Cheltenham,
Gloucestershire GL52 5EP
☎ +44 (0) 800 001 4466
www.kohler.co.uk