



KOHLER®


ALEO






	Bar
0.5 < 3 < 6	
	°C
55 < 60 < 65	



72292D-**






72293D-**





1




2




2




x2






x2






3







KOHLER®

US

Kohler Co.
444 Highland Drive
Kohler, WI 53044
© 1 800 456 4537
www.kohler.com

GB

Kohler UK
Cromwell Road, Cheltenham,
Gloucestershire GL52 5EP
© +44 (0) 800 001 4466
www.kohler.co.uk