

Thermostatic Built-In Shower Valve Trim,
with Temperature & Flow Control, for Modulo Valve

98726D / 98727D / 98729D

Product Description:	Thermostatic built-in shower valve with temperature & flow control - Trim only
	98726D-CP Aleo (1)
	98727D-CP Cuff (2)
	98729D-CP Strayt (3)
Required Item:	98699D-CP Modulo universal concealed box
Product Dimensions:	98726D-CP – W140 x H200 mm 98727D-CP – Diameter 200 mm 98729D-CP – W140 x 200 mm
Colour/Finish:	Polished Chrome
Material:	Brass Body
Pressure:	Minimum - 0.5 bar Maximum static - 8 bar Maintained - 4 bar
Product Weight (kg):	98726D-CP – 2.8 98727D-CP – 2.75 98729D-CP – 3.1
Guarantee (Years):	5
Dimensions (mm):	On following page

**Kohler UK**

Sales and Technical:

+44 (0) 844 571 0048 (Calls cost 7p per minute plus your phone company's access charge)

info@kohler.co.uk


www.KOHLER.co.uk

THE BOLD LOOK
OF **KOHLER**®



Thermostatic Built-In Shower Valve Trim,
with Temperature & Flow Control, for Modulo Valve

98726D / 98727D / 98729D



Dimensions (mm):



98726D-CP Aleo



98727D-CP Cuff



98729D-CP Strayt

