# Concealed Cistern Dual Flush 3/6L

E4324

OLI

Product Description: Concealed cistern dual flush 3/6L

Required Item: 8848K-CP Flush plate

**Product Dimensions:** W440 x H405 x D148 mm

Material: Polypropylene (PP)

Product Weight (kg): 3


Guarantee (Years): 10

Fixings Included: Yes

**Additional Information:** For under-window or inside low-wall installation.

The flush plate can be mounted on the front or on the top of the cistern.

### **Dimensions (mm)**



# Further information on following page



### **CISTERN:**

- Dual flush mechanical actuated
- Flush plate can be mounted front or top (cistern is supplied settled for front installation)
- Anti-condensation EPS Polysterene cove plate
- Easy installation
- Easy access for maintenance
- Silent AZOR float valve certificated according to the WRAS standard
- CE EN 14055 marking CL2
- Net pressure from 0.2 up to 20 bar
- Flush volumes: 3 litres (half flush) and 6 litres (full flush)
- Resistance to atmospheric humidity (Hr <90%)

### **ACCESSORIES:**

- 1 PP discharge pipe 68/45 with 315mm length
- 1 Protection sponge for stop valve
- 1 Stop-valve with mounting bracket
- 1 PP protection box
- 2 Fixing metal brackets with screws for wall mounting
- Installation instructions

