

Mira Virtue ER

Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Add classic, traditional design to your bathroom with the Mira Virtue ER. Its carefully crafted design features instantly make a statement and complete your traditional bathroom look, with spa-like deluge head.

Product Information

Description	Colour	Product No.
Mira Virtue ER	Chrome	1.1927.002

Features & Benefits

Temperature control

Thermostatic temperature control

Easy to fit

Quickly and easily fits onto reversed inlet supplies

Easy to service

Easily replaceable pull out large, long-life filters

Patented 'easy clip' system makes the cartridge easy to replace

1 spray 210mm deluge fixed showerhead with rub clean nozzles


For your customer

Single control for flow and temperature

Thermostatic temperature control and maximum temperature stop makes showering safer for entire family

Compatible with all systems, even at low pressure

Single spray 210mm deluge showerhead with rub clean nozzles



Product Specification

Tech Details

Temperature control

Control type: Thermostatic

Installation

Water entry points: Rising, falling or rear

Inlet connections: 15 mm compression (EV, BIV & BIR)

Outlet connections: ½" BSP Male Flat Face (EV) or 18mm compression (BIV & BIR)

Reversed inlets supported: Yes

Supply Conditions (hot and cold)

Cold water range: Up to 25°C

Hot water range: 60°C-65°C (recommended)

Minimum maintained pressure: 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Flow rate (Rain): 11.1 l/min at 0.5 bar,
Valve only: 17 l/min at 0.5 bar

Temperature stability: ± 2°C

Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe max temp: Factory set to 41°C

Adjustable maximum temperature for on-site conditions

Dimensions

