

Mira Minimal Dual Outlet

Mixer Shower

A compact, minimalist shower with handset and deluge head to enhance your shower experience



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Product Information

Description	Colour	Product No.
Mira Minimal Dual	Chrome	1.1943.002

Features & Benefits

Temperature control

Thermostatic temperature stability

Easy to fit

Pipe centers 50mm apart

Spanner free installation

Pipe spacer guide included to aid pipework installation during first fix

Front of tile installation system allows connection to pipework during second phase fix after tiling is complete

Multi-use tool supplied to aid installation

For your customer

Works on all systems, even at low pressure

Single sequential control for flow and temperature

Maximum temperature stop for increased safety (with override for a hotter shower)

Lever diverter control allows water to be diverted to either the shower handset or shower overhead or both

Mira Cool Shield™ to ensure valve doesn't get hot during showering

One spray 11cm showerhead with rub-clean nozzles

Large 20cm deluge showerhead with rub-clean nozzles

1.25m flexible shower hose

Swinging overhead riser

Valve retro fits over Mira Agile products



Product Specification

Tech Details

Temperature and flow control

Temperature control type: Thermostatic

Flow control type: Single sequential cartridge

Installation

Water entry points: Rear only

Inlet connections: Direct 15mm push fit connections

Outlet connections: ½" BSP Male

Reversed inlets supported: No = hot left, cold right only

Supply Conditions (hot and cold)

Cold water range: 1°C to 25°C

Hot water range: Min 55°C; 60°C - 65°C (recommended)

Minimum maintained pressure (gas water heater) : 1 bar (10 metre head)

Minimum maintained pressure (gravity system) : 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Flow rate (at handset): 9 l/min at 0.5 bar, (at deluge): 10.5 l/min

Flow regulator: 6 l/min (supplied with product - x2)

Temperature stability: ± 2°C

Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe max temp

Adjustable maximum temperature for on-site conditions

Approvals

KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)

TMV2 approved product



Dimensions

