

Mira Beacon Dual

Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Brighten your day with sleek, built-in style design and our innovative warm-up indicator



Product Information

Description	Colour	Product No.
Mira Beacon Dual	Chrome	1.1944.001

Features & Benefits

Temperature control

Thermostatic temperature stability

Easy to fit

Pipe centers 50mm apart

Spanner free installation

Pipe spacer guide included to aid pipework installation during first fix
Front of tile installation system allows connection to pipework during second phase fix after tiling is complete

Multi-use tool supplied to aid installation

For your customer

Works on all systems, even at low pressure

Separate flow and temperature controls using button actuation

Maximum temperature stop for increased safety (with override for a hotter shower)

Choose your outlet - intuitive push button technology allows you to select the handset, overhead or both

Mira Cool Shield™ to ensure valve doesn't get hot during showering

Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

One spray 11cm multi-mode showerhead with rub-clean nozzles

Large 25cm deluge showerhead with rub-clean nozzles

1.25m flexible shower hose

The latest illuminating technology, no wiring or batteries required.
Mira HydroGlo™ delivers extra experiences with no extra hassle.

Retro fits over Mira Agile products

Product Specification

Tech Details

Temperature and flow control

Temperature control type: Thermostatic

Flow actuation: Push button

Installation

Water entry points: Rear only

Inlet connections: Direct 15mm push fit connections

Outlet connections: ½" BSP Male

Reversed inlets supported: No = hot left, cold right only

Supply Conditions (hot and cold)

Cold water range: 1°C to 25°C

Hot water range: Min 55°C; 60°C - 65°C (recommended)

Minimum maintained pressure (gas water heater) : 1 bar (10 metre head)

Minimum maintained pressure (gravity system) : 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Flow rate (at handset): 7.6 l/min at 0.5 bar, (at deluge): 9.9 l/min

Flow regulator: 9 l/min (supplied with product - x2)

Temperature stability: ± 2°C

Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe max temp

Adjustable maximum temperature for on-site conditions

Approvals

KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)

TMV2 approved product



Dimensions

