

Mira Adept BIV & Adept Eco BIV

Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Contemporary, sleek design delivering the ultimate performance, and Adept Eco BIV has water-saving technology.



Product Information

Description	Colour	Product No.
Mira Adept BIV	Chrome	1.1736.404
Mira Adept Eco BIV	Chrome	1.1736.423

Features & Benefits

Temperature control

Thermostatic temperature stability

Easy to fit

Miniature valve body, plus plastic backplate for easy mounting to wall

Variable valve building in depth between 51mm-70mm

2nd fix tile-mounted outlet for the hose

Easy to service

Large, long-life filters and replaceable cartridge

For your customer

Separate flow and temperature controls

Mira Adept BIV has Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

Mira Adept Eco BIV has a 6l/min flow regulator to save water and energy

4 spray 9cm showerhead with rub-clean nozzles

Product Specification

Technical Details

Temperature control

Control type: Thermostatic

Installation

Water entry points: side only

Inlet connections: 15 mm compression

Outlet connections: 15 mm compression top outlet

Reversed inlets supported: No = hot left, cold right only

Supply Conditions (hot and cold)

Cold water range: Up to 25°C

Hot water range: 50°C-65°C

Minimum maintained pressure: 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Flow rate (at handset): Adept BIV, 13 l/min at 0.5 bar; Adept Eco BIV, 6 l/min at 0.5 bar

Temperature stability: $\pm 2^\circ\text{C}$

Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe max temp: Factory set to 43°C

Approvals

KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)

Buildcert TMV2 Approved



Dimensions

