

Mira Agile ERD

Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Compact design with maximum performance. Enjoy the greater coverage of a deluge showerhead and the practicality of a handshower.



Product Information

Description	Colour	Product No.
Mira Agile ERD	Chrome	1.1736.403

Features & Benefits

Temperature control

Thermostatic temperature control makes showering safer for all the family

Easy to fit

Spanner-free installation

Pipe and tiling templates included

Patented in-valve push fit connection

Pipe centres 50mm apart

Adjustable slide bar fixings

Easy to service

Large, long-life filters and replaceable cartridge

For your customer

Separate temperature and flow controls

Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

25cm deluge fixed head plus separate 11cm 4 spray showerhead

Divert between the two heads or have both on at the same time

Product Specification

Technical Details

Temperature control

Thermostatic temperature control

Adjustable maximum temperature for on-site conditions

Installation

Water entry points: rear only

Inlet connections: 15 mm copper pipe

Outlet connections: ½" BSP Male Flat Face

Reversed inlets supported: No = hot left, cold right only

Supply Conditions (hot and cold)

Cold water range: Up to 25°C

Hot water range: 55°C-85°C (55°C-65°C recommended)

Minimum maintained pressure: 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Flow rate (at handset): 13 l/min at 0.5 bar; (at deluge) 11.3 l/min at 0.5 bar; (combined) 15.9 l/min at 0.5 bar

Temperature stability: ± 2°C

Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe max temp: Factory set to 43°C

Approvals

KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)

Buildcert TMV2 Approved



Dimensions

