

Mira Agile Sense ERD+

Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Enjoy the greater coverage of a deluge showerhead and the practicality of a handshower. Includes integrated Sense module which displays time and temperature for precise control.

Product Information

Description	Colour	Product No.
Mira Agile Sense ERD+	Chrome	1.1928.002

Features & Benefits

Temperature control

Thermostatic temperature control makes showering safer for all the family

Easy to fit

Spanner-free installation

Pipe and tiling templates included

Patented in-valve push fit connection

Pipe centres 50 mm apart

Easy to service

Replaceable cartridge

For your customer

Single control for flow and temperature

Integrated Mira Sense module displays time and temperature

Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

250 mm deluge fixed head plus separate 110 mm 4 spray showerhead

Divert between the two heads or have both on at the same time



Product Specification

Technical Details

Temperature control

Thermostatic temperature control

Adjustable maximum temperature for on-site conditions

Installation

Water entry points: rear only

Inlet connections: 15 mm copper pipe

Outlet connections: ½" BSP Male Flat Face

Reversed inlets supported: No = hot left, cold right only

Supply Conditions (hot and cold)

Cold water range: 1°C to 25°C

Hot water range: 55°C-65°C (recommended for optimum performance)

Minimum maintained pressure: 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

For optimum performance supplies should be nominally equal.

Performance

Flow rate (at handset): 9.5 l/min at 0.5 bar; (at deluge) 11.5 l/min at 0.5 bar; (combined) 14 l/min at 0.5 bar

Temperature stability: ± 2°C

Safety Features

Automatic shutdown: Shutdown within 2 secs should either supply fail

Factory set to safe max temp: Factory set to 43°C

Approvals

KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)

Buildcert TMV2 Approved



Dimensions

