

Mira Agile Store EV+

Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Compact design with maximum performance. Includes handy storage module for clutter-free showering.



Product Information

Description	Colour	Product No.
Mira Agile Store EV+	Chrome	1.1928.004

Features & Benefits

Temperature control

Thermostatic temperature control makes showering safer for all the family

Easy to fit

Spanner-free installation

Pipe and tiling templates included

Patented in-valve push fit connection

Pipe centres 50 mm apart

Adjustable slide bar fixings

Easy to service

Replaceable cartridge

For your customer

Single control for flow and temperature

Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

Large 4 spray 110 mm showerhead with rub-clean nozzles for a greater showering experience

Adjustable slide bar fixings

Product Specification

Technical Details

Temperature control

Control type: Thermostatic temperature control

Installation

Water entry points: rear only

Inlet connections: 15 mm copper pipe

Outlet connections: ½" BSP Male Flat Face

Reversed inlets supported: No = hot left, cold right only

Supply Conditions (hot and cold)

Cold water range: 1°C to 25°C

Hot water range: 55°C-65°C (recommended for optimum performance)

Minimum maintained pressure: 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

For optimum performance supplies should be nominally equal.

Performance

Flow rate (at handset): 11 l/min at 0.5 bar

Temperature stability: ± 2°C

Safety Features

Automatic shutdown: Shutdown within 2 secs should either supply fail

Factory set to safe max temp: Factory set to 43°C

Approvals

KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)

Buildcert TMV2 Approved



Dimensions

