

# Mira Azora

## Electric Shower



Frosted glass fascia complemented by chrome features. Stylish design combined with safe, thermostatic technology.



### Product Information

Description	Colour	Product No.
Mira Azora 9.8kW	Frosted Glass	1.1634.011

### Features & Benefits

#### Temperature control

Thermostatic temperature control

#### Easy to fit

Retrofits onto inlets of most Mira electric showers

#### Easy to service

Easy filter access

#### For your customer

Separate power and temperature controls

Push button on/off, with choice of 3 flow settings

Mira Sensi-flo™ technology helps prevent scalding

Mira Clearscale™ and Dual Element™ technology reduces limescale by up to 50%

Phased shutdown flushes hot water from the tank making it safe for the next user

4 spray 11cm showerhead with rub-clean nozzles

# Product Specification

## Tech Details

### Temperature control

Control type: Thermostatic SMA

### Installation

Power options: 9.8kW 240V AC (9.0kW 230V AC)

Supply voltage: 230v  $\pm$  10%

Supply rating: 45 amp (9.8kW)

Terminal Block connections: Maximum 16mm<sup>2</sup>

Water entry points: Left (rising, falling & rear)

Cable entry points: Left (rising, falling & rear)

Inlet connections: Brass inlet connector. 15mm compression fitting

Outlet connections: 1/2" BSP Male

### Supply Conditions

Minimum maintained pressure: 0.7 bar (7 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

### Performance

Temperature stability:  $\pm$  2°C

### Safety Features

Phased shutdown: Yes

Factory set to safe max temp: Factory set at 48°C

Mira Sensi-flo™: Yes

### Accessories

Wide range of accessories available at [www.mirashowers.co.uk](http://www.mirashowers.co.uk)

### Approvals

Energy Efficiency: Class A



## Dimensions

