

Mira Corus

Electric Shower



An affordable, stylish electric shower with easy to use controls.



Product Information

Description	Colour	Product No.
Mira Corus 8.5 kW	White/Chrome	1.1895.007
Mira Corus 9.5kW	White/Chrome	1.1895.008
Mira Corus 10.8kW	White/Chrome	1.1895.009

Features & Benefits

Temperature control

Pressure stabilised temperature control

Easy to fit

Left-hand water and cable entry points

Adjustable slide bar fits over holes left by previous shower kit

Easy to service

Easy filter access

For your customer

Separate power and temperature controls.

Push button on/off

Three power settings

Mira Clearscale™ reduces limescale by up to 50%

110mm 4 spray showerhead with rub-clean nozzles

Modern aesthetics with chrome detailing

Product Specification

Tech Details

Temperature control

Control type: Pressure stabilised

Installation

Power options: 8.5kW 240V AC (7.8kW 230V AC) • 9.5kW 240V AC (8.7kW 230V AC) • 10.8kW 240V AC (9.9kW 230V AC)

Supply voltage: 230v ± 10%

Supply rating: 40 amp (8.5 & 9.5kW); 45 amp (10.8kW)

Terminal Block connections: Maximum 16mm²

Water entry points: Left (rising, falling & rear)

Cable entry points: Left (rising, falling & rear)

Inlet connections: 15mm plastic stub, compression or push-fit fittings

Outlet connections: ½" BSP Male

Supply Conditions

Minimum maintained pressure: 8.5 & 9.5kW: 0.7 bar (7 metre head); 10.8kW: 1.0 bar (10 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Temperature stability: ± 6°C

Safety Features

Phased shutdown: No

Factory set to safe max temp: No

Mira Sensi-flo™: No

Accessories

Wide range of accessories available at www.mirashowers.co.uk

Approvals

Energy Efficiency: Class A



Intertek

Dimensions

