

# Mira Platinum Dual

## Digital Mixer



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Experience ultimate control at your fingertips with our easy to use, wireless Platinum Dual controller.

### Product Information

Description	Colour	Product No.
Mira Platinum Dual Shower, Rear Fed (High Pressure/Combi)	Chrome	1.1796.003
Mira Platinum Dual Shower, Rear Fed (Pumped for Gravity)	Chrome	1.1796.004
Mira Platinum Dual Shower, Ceiling Fed (HP/Combi)	Chrome	1.1796.001
Mira Platinum Dual Shower, Ceiling Fed (Pumped for Gravity)	Chrome	1.1796.002
Mira Platinum Dual Shower, Valve & Controller Only (HP/Combi)	Chrome	1.1796.005
Mira Platinum Dual Shower, Valve & Controller Only (Pumped)	Chrome	1.1796.006

### Features & Benefits

#### Temperature control

Thermostatic temperature stability with digital intelligence

Maximum temperature setting for increased safety

#### Easy to fit & maintain

Rear and ceiling fed options available for all types of installation

Built in push-fit isolators

Large long-life filters and replaceable cartridge

#### For your customer

Adjust your temperature at the touch of a button, and rotate the controller to fine tune your flow

Warm-up mode pauses at your ideal temperature so it's ready when you are

Digital clock display with 5 minute timer when the Eco function is selected

Includes Mira 360 showerhead with Mira Flipstream™ technology - 1 flip action, 4 unique sprays, plus a 25cm deluge head

Turn your shower on before you get in with an optional secondary controller, useable from up to 10m away



MIRA PLATINUM  
REAR FED



MIRA PLATINUM  
CEILING FED

# Product Specification

## Tech Details

### Installation Units & Fittings

Water Entry Points - Back, Rear Fed; Top, Ceiling Fed  
 Inlet Connections: 15mm Push Fit (supplied) or 15mm compression  
 Data Connection to Digital Mixer: Wireless

### Digital Mixer

Inlet Connections: 15mm Push Fit (supplied) or 15mm compression  
 Outlet connection: 15mm push fit (supplied)  
 Data Connection to control unit and fittings: Wireless  
 Supply voltage: 230v +10%  
 Supply rating: 3 amp

### Supply Conditions

Cold water range: 1°C-20°C  
 Hot water range: 55°C-65°C  
 Minimum maintained pressure:  
 Pumped: 0.01 bar (10cm head); High Pressure: 0.5 bar (5 metre head)  
 Maximum maintained pressure:  
 Pumped: 1.0 bar (10 metre head); High Pressure: 5.0 bar (50 metre head)  
 Maximum static pressure:  
 Pumped: 1.0 bar (10 metre head); High Pressure: 10.0 bar (100 metre head)

### Performance

Flow rate: up to 16 l/min at 0.1 bar (Pumped); 1 bar (High Pressure)  
 Temperature stability: ± 1°C

### Safety Features

Factory set to safe max temp: Factory set at 45°C  
 Automatic shutdown: Yes

### Approvals

WRAS approved  
 KIWA UK approved product



## Dimensions

