

# Mira Reflex ERD

## Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

A sleek design and delivers a consistently great performance from both the deluge and handset showerheads.



### Product Information

Description	Colour	Product No.
Mira Reflex ERD	Chrome	2.1878.004

### Features & Benefits

#### Temperature control

Thermostatic temperature stability

#### Easy to fit

Front of tile installation system

#### Easy to service

Large, long-life filters and replaceable cartridge

#### For your customer

Separate flow and temperature controls

Maximum temperature stop for increased safety (with override for a hotter shower)

Mira Cool Shield™ to ensure valve doesn't get hot during showering

Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

1 spray 9cm showerhead with rub-clean nozzles

Large 200mm deluge showerhead

# Product Specification

## Technical Details

### Temperature control

Control type: Thermostatic

### Installation

Water entry points: rear only (bar valve exposed pipework installation elbows available for rising or falling inlets)

Inlet connections: 1/2" BSP to pipework, 3/4" BSP to shower unit

Outlet connections: 1/2" BSP Male

Adjustable pipe centres: 150mm ± 24mm

Reversed inlets supported: No = hot left, cold right only

### Supply Conditions (hot and cold)

Cold water range: Up to 25°C

Hot water range: 60°C - 65°C

Minimum maintained pressure: 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

### Performance

Flow rate (at handset): 10.2 l/min at 0.5 bar

Temperature stability: ± 2°C

### Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe max temp: Factory set to 41°C

Adjustable maximum temperature for on-site conditions

### Approvals

KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)



## Dimensions

