

Mira Relate EV

Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

A sleek, stylish design and with a consistently genuine performance.



Product Information

Description	Colour	Product No.
Mira Relate EV	Chrome	2.1878.001

Features & Benefits

Temperature control

Thermostatic temperature stability

Easy to fit

Front of tile installation system

Slide bar with adjustable fixing centres (400-510mm)

Easy to service

Large, long-life filters and replaceable cartridge

For your customer

Separate flow and temperature controls

Maximum temperature stop for increased safety (with override for a hotter shower)

Mira Cool Shield™ to ensure valve doesn't get hot during showering

Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

1 spray 9cm showerhead with rub-clean nozzles

Product Specification

Technical Details

Temperature control

Control type: Thermostatic

Installation

Water entry points: rear only (bar valve exposed pipework installation elbows available for rising or falling inlets)

Inlet connections: 1/2" BSP to pipework, 3/4" BSP to shower unit

Outlet connections: 1/2" BSP Male

Adjustable pipe centres: 150mm ± 24mm

Reversed inlets supported: No = hot left, cold right only

Supply Conditions (hot and cold)

Cold water range: Up to 25°C

Hot water range: 60°C - 65°C

Minimum maintained pressure: 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Flow rate (at handset): 10.2 l/min at 0.5 bar

Temperature stability: ± 2°C

Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe max temp: Factory set to 41°C

Adjustable maximum temperature for on-site conditions

Approvals

KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)



Dimensions

