

# Mira Select EV

## Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

A great choice for families with its thermostatic control providing genuine performance, even at low pressure.



### Product Information

Description	Colour	Product No.
Mira Select EV	Chrome	1.1592.005

### Features & Benefits

#### Temperature control

Thermostatic temperature stability

#### Easy to fit

Quickly and easily fits onto reversed inlet supplies.

Adjustable inlets (149-154mm)

#### Easy to service

Large, long-life filters and replaceable cartridge

#### For your customer

Separate flow and temperature controls

Maximum temperature stop for increased safety

Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

4 spray 9cm showerhead with rub-clean nozzles

# Product Specification

## Tech Details

### Temperature control

Control type: Thermostatic

### Installation

Water entry points: Rising, falling or rear

Inlet connections: 15 mm compression

Outlet connections: 15 mm compression or ½" BSP Male Flat Face

Reversed inlets supported: Yes

Adjustable pipe centres: 149-154mm

### Supply Conditions (hot and cold)

Cold water range: Up to 25°C

Hot water range: 50°C-85°C (operating)  
55°C-65°C (recommended)

Minimum maintained pressure: 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

### Performance

Flow rate (at handset): 10 l/min at 0.5 bar

Temperature stability: ± 1°C

### Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe max temp: Factory set to 41°C

Adjustable maximum temperature for on-site conditions

### Approvals

WRAS approved (Water Regulations Advisory Scheme)



## Dimensions

