

Mira Sport Multi-Fit™

Electric Shower Range



Ideal for replacing an existing electric shower, offering multiple cable and water entry points, reducing the need for re-tiling.



Product Information

Description	Colour	Product No.
Mira Sport Multi-Fit 9.0kW	White/Chrome	1.1746.009
Mira Sport Multi-Fit 9.8kW	White/Chrome	1.1746.010

Features & Benefits

Temperature control

Advanced pressure stabilised temperature control

Easy to fit

Retrofits Triton, Aqualisa, Creda, Bristan and all Mira electric showers

Adjustable slide bar fits over holes left by previous shower kit

Easy to service

Easy filter access

For your customer

Separate power and temperature controls.

Push button on/off

Mira Sensi-flo™ technology helps prevent scalding

Mira Clearscale™ and Dual Element™ technology reduces limescale by up to 50%

Phased shutdown flushes hot water from the tank making it safe for the next user

4 spray 11cm showerhead with rub-clean nozzles

Product Specification

Tech Details

Temperature control

Control type: Advanced pressure stabilised

Installation

Power options: 9.0kW 240V AC (8.3kW 230V AC) • 9.8kW 240v AC (9.0kW 230V AC)

Supply voltage: 230v ± 10%

Supply rating: 40 amp (9.0kW); 45 amp (9.8kW)

Terminal Block connections: Maximum 16mm²

Water entry points: Left or right (rising, falling or rear)

Cable entry points: Left or right (rising, falling or rear)

Inlet connections: LEFT: Brass inlet connector. 15mm compression fitting / RIGHT: 15mm plastic swivel stub compression or push fitting

Outlet connections: ½" BSP Male

Supply Conditions

Minimum maintained pressure: 9.0 & 9.8kW: 0.7 bar (7 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Temperature stability: ± 6°C

Safety Features

Phased shutdown: Yes

Factory set to safe max temp: No

Mira Sensi-flo™: Yes

Accessories

Wide range of accessories available at www.mirashowers.co.uk

Approvals

Energy Efficiency: Class A



Dimensions

