

# Mira Vision Flex

## Digital Shower Range



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Easy to operate, precise temperature control and an extra long, easy glide slide bar and a 2m hose - it's the ultimate in flexibility.

### Product Information

Description	Colour	Product No.
Mira Vision Flex – High Pressure	White/Chrome	3.1797.111
Mira Vision Flex – Pumped	White/Chrome	3.1797.112

### Features & Benefits

#### High Performance

High flow rates and wireless control

#### Temperature control

Thermostatic temperature stability with digital intelligence

#### Easy to fit

Can be fully installed in as little as a couple of hours

#### Easy to service

Large, long-life filters and replaceable cartridge

#### For your customer

Separate, push button controls for start/stop, flow and temperature adjustment

Programmable to suit your lifestyle – warm-up mode, eco setting and clock display

Keep track of the time – displays a 5 minute timer when Eco function is selected

Warm-up mode pauses at your ideal temperature until you are ready to get in

Easy glide and extra long slide bar – can be adjusted with one hand

Extra showerhead parking socket for additional flexibility

Everclear showerhead resists limescale build-up



# Product Specification

## Tech Details

### Temperature control

Control type: Thermostatic

### Installation – Control Units and Shower Fittings

Water entry points: Back (rear fed)

Inlet connections: 15mm push fit (supplied) or 15mm compression

Data connection to digital mixer: Wireless

### Installation – Digital Mixer

Inlet connections: 15mm push fit (supplied) or 15mm compression

Outlet connections: 15mm push fit (supplied)

Data connection to control unit & fittings: Wireless

Power supply unit to Digital Mixer connection: Power supply unit built into Mixer Valve unit

Supply voltage: 230v ± 10%

Supply rating: 3 amp

### Supply Conditions

Cold water range: 1°C-20°C

Hot water range: 55°C-65°C

Minimum maintained pressure: Pumped: 0.01 bar(10cm head); High pressure: 0.5 bar (5 metre head)

### Supply Conditions – continued

Maximum maintained pressure: Pumped: 1.0 bar(10 metre head); High pressure: 5.0 bar (50 metre head)

Maximum static pressure: Pumped: 1.0 bar (10 metre head); High pressure: 10.0 bar (100 metre head)

### Performance

Flow rate (open outlet): 16 l/min at 1 bar

Temperature stability: ± 1°C

### Safety Features

Factory set to safe max temp: Factory set to 45°C

### Approvals

WRAS approved

BEAB approved (High Pressure only)

KIWA UK approved product



**Intertek**

## Dimensions

