

# MIRA MINIDUO

Part Number: EV, Chrome: 1.1663.004  
 Part Number: BIV, Chrome: 1.1663.008

SAVES SPACE – SMALLER THAN A NORMAL MIXER

### HIGH PERFORMANCE

Magni-Flo™ gives up to 3x more flow

### TEMPERATURE CONTROL

Thermostatic temperature stability

### EASY TO FIT

Quickly and easily fits onto reversed inlet supplies

### EASY TO SERVICE

Large, long-life filters and replaceable cartridge

### FOR YOUR CUSTOMER

Separate flow and temperature controls

4 spray 9 cm showerhead with rub clean nozzles

MIRA MINIDUO EV

MIRA MINIDUO BIV



## TECH DETAILS

### TEMPERATURE CONTROL

Control type: Thermostatic

### INSTALLATION

Water entry points: Rising, falling or rear

Inlet connections: 15 mm compression (EV & BIV)

Outlet connections: ½" BSP Male Flat Face (EV); 15 mm compression (BIV)

Reversed inlets supported: Yes

### SUPPLY CONDITIONS (hot and cold supplies to be at nominally equal pressure)

Cold water range: Up to 25°C

Hot water range: 50°C-85°C (operating); 55°C-65°C (recommended)

Minimum maintained pressure: 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

### PERFORMANCE

Flow rate (at handset): 11 l/min at 0.5 bar

Temperature stability: ± 2°C

### SAFETY FEATURES

Automatic Shutdown: Shutdown to seepage in 2 seconds


Factory set to safe max temp: Factory set to 41°C

Adjustable maximum temperature for on-site conditions

### ACCESSORIES

Mini valve retrofit kit available to fit pipe centres between 133-153 mm (see page 19)

## TECH DRAWINGS



See Magni-Flo™ in action by scanning this QR code

