

MIRA MINIDUO WITH ECO SHOWERHEAD

Part Number: EV, Chrome: 1.1663.241
 Part Number: BIV, Chrome: 1.1663.242
 Part Number: BIR, Chrome: 1.1663.243

SAVES SPACE – SMALLER THAN A NORMAL MIXER

SAVES WATER

Ecoefficient™ – saves up to 75% water compared to Miniduo

TEMPERATURE CONTROL

Thermostatic temperature stability

EASY TO FIT

Quickly and easily fits onto reversed inlet supplies

EASY TO SERVICE

Large, long-life filters and replaceable cartridge

FOR YOUR CUSTOMER

Separate flow and temperature controls

3 spray 9 cm showerhead with rub clean nozzles



MIRA MINIDUO WITH ECO SHOWERHEAD EV

MIRA MINIDUO WITH ECO SHOWERHEAD BIR



TECH DETAILS

TEMPERATURE CONTROL

Control type: Thermostatic

INSTALLATION

Water entry points: Rising, falling or rear

Inlet connections: 15 mm compression (EV, BIV & BIR)

Outlet connections: ½" BSP Flat Face (EV) or 15 mm compression (BIV & BIR)

Reversed inlets supported: YES

SUPPLY CONDITIONS (hot and cold supplies to be at nominally equal pressure)

Cold water range: Up to 25°C

Hot water range: 50°C-85°C (operating); 55°C-65°C (recommended)

Minimum maintained pressure: 0.5 bar (5 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

PERFORMANCE

Flow rate (at handset): 6 l/min at 0.5 bar

Temperature stability: ± 2°C

SAFETY FEATURES

Automatic Shutdown: Shutdown to seepage in 2 seconds

Factory set to safe max temp: Factory set to 41°C

Adjustable maximum temperature for on-site conditions

ACCESSORIES

Extended elbows pack available for EV to fit to 133-153 mm pipe centres – see page 19

See how much water it saves by scanning this QR code



TECH DRAWINGS

